



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CT11NT50C Cable Tie CT11NT50-C, 10 Bags/Case

Minnesota Mining (3M)

|                  |  |
|------------------|--|
| Catalog Number   | CT11NT50C  |
| Manufacturer     | Minnesota Mining (3M)  |
| Description      | Cable Tie, 3 In;76.2 MM Bundle Diameter, Natural, 11.1 In;282 MM Length, Made In Usa, Nylon 6/6 Material, +185°F;+85°C Maximum Operating Temperature, -40°C;-40°F Minimum Operating Temperature, 100 BG Package Quantity, Weather Resistant Resistance Properties, Culus Listed;Rohs Compliant;UI Listed 181B-C;UI Listed Type 21/Type 21S;UI Standard 62275;UI. File # E116841, Self-Adhesive Style, 22.68 KG;220 NM;50 LB Tensile Strength, 0.05 In;1.3 MM Thickness, 0.18 In;4.6 MM Width |
| Weight per unit  | 0.0004 (lbs/each)  |
| Product Category | Cable Ties & Wraps   |

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | CABLE TIE CT11NT50-C, 10 BAGS/CASE  |
| extra long description | 3M 7000031856 3M™ Standard Nylon Ca |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| GTIN                      | 00051128593028 |
| Manufacturers Part Number | CT11NT50-C     |
| UPC                       | 051128593028   |

### Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
|----------------------|----------------------------|

### Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 100    |
| Package         | 1000   |
| Weight Per each | 0.0004 |