



Powering Business Worldwide

pe.eaton.com

Locking Receptacle

CWL515R

UPC:040893676845

Dimensions:

- **Height:** 4.52 IN
- **Length:** 1.79 IN
- **Width:** 1.91 IN

Warranties: No Data

Specifications:

- **Special Features:** #REF!
- **Allowable Wire Size:** #14-8 AWG
- **Amperage Rating:** 15A
- **Application:** Industrial
- **Voltage Rating:** 125V
- **Wiring Method:** Back and side
- **Color:** Black
- **Design Type:** Single
- **Nema Configuration:** L5-15
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Material:** Glass-filled nylon
- **Operating Temperature:** -40° to 115°C

Supporting documents: No Data

Certifications: No Data

Product compliance:

- RoHS Compliant

