



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DG134061FNC21C DG1 480V FR4 N1 40HP 61A CT 50HP 72A VT

Eaton Corp

Catalog Number	DG134061FNC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 61A 400V Input Three-Phase Mains Connection/Three-Phase Motor Connection Internal Emc Filter Graphic LCD Display and Keypad , Nema 1
Weight per unit	77.5 (lbs/each)
Product Category	Ac Drives

### Features

display	LCD graphical
Input Voltage	400 V

### Dimensions and Weight

Depth	15
Height	18.5
Width	28

### Descriptions

Description	DG1 480V FR4 N1 40HP 61A CT 50HP 72A VT
extra long description	ETN DG1-34061FN-C21C DG1,480V FR4 ,
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 61A 400V input Three-phase mains connection/three-phase motor connection Internal EMC filter Graphic LCD display and keypad , NEMA 1
Product Type	DG1, 480V FR4 , N1, 40HP, 61A CT, 50HP, 72A VT

### Manufacturer Information

Brand	Eaton
GTIN	00786685878812
Manufacturers Part Number	DG1-34061FN-C21C
UPC	786685878812

### Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	77.5

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL cULCE IEC/EN 61800-5-1 IEC 61800-5-2 UL 508C IEC 61508 EN 62061 EN ISO 13849-1,CE Marked,RoHS Compliant,C-Tick Compliant