



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG1344D3FBC21C DG1 480V FR1 N1 2HP 4.3A CT 3HP 5.6A VT W/ BC Eaton Corp

Catalog Number	DG1344D3FBC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 380-500V Input 1.5 KW 2 HP CT 3PH 50/60 HZ 4.3A Output IP21/Type 1 Enclosure FR1 LCD Display Internal Emc Filter and DC Choke Ethernet
Weight per unit	16.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	400 V, 380-500 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	17.3
Height	12.7
Width	9

Descriptions

Description	DG1 480V FR1 N1 2HP 4.3A CT 3HP 5.6A VT W/ BC
extra long description	ETN DG1-344D3FB-C21C DG1,480V FR1 ,
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 380-500V input 1.5 kW 2 Hp CT 3PH 50/60 Hz 4.3A output IP21/type 1 enclosure FR1 LCD display Internal EMC filter and DC choke EtherNet
Product Type	DG1, 480V FR1 , N1, 2HP, 4.3A/3HP, 5.6A, BC

Manufacturer Information

Brand	Eaton
GTIN	00786685878843
Manufacturers Part Number	DG1-344D3FB-C21C
UPC	786685878843

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	16

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	IP21/type 1 enclosure EN ISO 13849-1,UL Listed,cUL Listed,EN 61800-3,UL 508C,EN 62061,EN 61800-5-1,IEC 61508,CE Marked,RoHS Compliant,C-Tick Compliant,GoST-R