



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH363NGK 100A/3P HD Fusible Safety Switch 600V W/Neut Nema1

Eaton Corp

Catalog Number	DH363NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 100 A, Nema 1, Painted Steel, Class H, Fusible With Neutral, Three-Pole, Four-Wire, 600 V, Max HP: 30, 40/ 60, 75 HP (1/3PH @480, 600 V), #14-#1/0 Cu/Al
Weight per unit	23.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	100
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	600 V

Dimensions and Weight

Depth	22.5
Height	9
Width	12.75

Descriptions

Description	100A/3P HD FUSIBLE SAFETY SWITCH 600V W/NEUT NEMA1
extra long description	ETN DH363NGK 100A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 100 A, NEMA 1, Painted steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0 Cu/Al
Product Type	100A/3P HD FSBL Sfty SW 600V W/Neut N1

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206486
Manufacturers Part Number	DH363NGK
UPC	782113206486

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	23

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	1
standard	UL Listed, NEC 230.62 (C) Compliant Barrier