

# Specifications



## Eaton DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386

### General specifications

<b>PRODUCT NAME</b>	Eaton decorator dimmer
<b>CATALOG NUMBER</b>	DI06P-W
<b>UPC</b>	032664662386
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	4.25 in
<b>PRODUCT WIDTH</b>	2 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	NOM cULus Listed

## Product specifications

<b>FREQUENCY RATING</b>	60 Hz
<b>SPECIAL FEATURES</b>	Preset feature
<b>TYPE</b>	Dimmer
<b>VOLTAGE RATING</b>	120 V
<b>POWER CONSUMPTION</b>	600 W
<b>WIRING METHOD</b>	Back and side
<b>ENVIRONMENTAL CONDITIONS</b>	Indoor
<b>SWITCH TYPE</b>	Single-pole, three-way
<b>LOAD TYPE</b>	INC MLV HAL
<b>HOUSING</b>	Polycarbonate
<b>TORQUE RATING</b>	14 lbf-inch
<b>MATERIAL</b>	Polycarbonate
<b>ACTUATOR</b>	Slide
<b>COLOR</b>	White
<b>CONNECTION TYPE</b>	Wire lead

## Resources

<b>BROCHURES</b>	<a href="#">Wiring Devices Buyer's Guide</a>
<b>INSTALLATION VIDEOS</b>	<a href="#">How to install Eaton's universal slide dimmers</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - DI06P-W</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386

### General specifications

<b>PRODUCT NAME</b>	Eaton decorator dimmer
<b>CATALOG NUMBER</b>	DI06P-W
<b>UPC</b>	032664662386
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	4.25 in
<b>PRODUCT WIDTH</b>	2 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	NOM cULus Listed

## Product specifications

<b>FREQUENCY RATING</b>	60 Hz
<b>SPECIAL FEATURES</b>	Preset feature
<b>TYPE</b>	Dimmer
<b>VOLTAGE RATING</b>	120 V
<b>POWER CONSUMPTION</b>	600 W
<b>WIRING METHOD</b>	Back and side
<b>ENVIRONMENTAL CONDITIONS</b>	Indoor
<b>SWITCH TYPE</b>	Single-pole, three-way
<b>LOAD TYPE</b>	INC MLV HAL
<b>HOUSING</b>	Polycarbonate
<b>TORQUE RATING</b>	14 lbf-inch
<b>MATERIAL</b>	Polycarbonate
<b>ACTUATOR</b>	Slide
<b>COLOR</b>	White
<b>CONNECTION TYPE</b>	Wire lead

## Resources

<b>BROCHURES</b>	<a href="#">Wiring Devices Buyer's Guide</a>
<b>INSTALLATION VIDEOS</b>	<a href="#">How to install Eaton's universal slide dimmers</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - DI06P-W</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

