

Specifications



Eaton DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386

General specifications

PRODUCT NAME	Eaton decorator dimmer
CATALOG NUMBER	DI06P-W
UPC	032664662386
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	NOM cULus Listed

Product specifications

FREQUENCY RATING	60 Hz
SPECIAL FEATURES	Preset feature
TYPE	Dimmer
VOLTAGE RATING	120 V
POWER CONSUMPTION	600 W
WIRING METHOD	Back and side
ENVIRONMENTAL CONDITIONS	Indoor
SWITCH TYPE	Single-pole, three-way
LOAD TYPE	INC MLV HAL
HOUSING	Polycarbonate
TORQUE RATING	14 lbf-inch
MATERIAL	Polycarbonate
ACTUATOR	Slide
COLOR	White
CONNECTION TYPE	Wire lead

Resources

BROCHURES	Wiring Devices Buyer's Guide
INSTALLATION VIDEOS	How to install Eaton's universal slide dimmers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - DI06P-W

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

