



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **DR20WHI Deco RCPT, Comm GRD, 20A 125V, 5-20R, WH** *Hubbell Wiring Devices*

Catalog Number	DR20WHI
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Decorator, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	90090
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

### **Dimensions and Weight**

Size	3.28 in x 1.06 in x 1.29 in
------	-----------------------------

### **Descriptions**

Description	DECO RCPT, COMM GRD, 20A 125V, 5-20R, WH
extra long description	HWDK DR20WHI DECO RCPT, COMM GRD, 2
Long Description	Straight Blade Devices, Receptacles, Duplex, Decorator, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, White, Single Pack.
Product Type	Deco RCPT, Comm GRD, 20A 125V, 5-20R, WH
Special Features	Self Grounding

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585127903
Manufacturers Part Number	DR20WHI
series	Commercial Specification Grade
UPC	783585127903



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Standard Duplex

## Packaging

Carton	1
Package	10
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42; Fed. Spec. W-C-596; NEMA® WD-6 Compliant; UL Listed to UL498 File No. E2186