

**NEW!**  
KITS on reverse

# WIRE GRABBER™

*Hanging Support for Fixtures and More, Up to 75 lbs.*



**NEW**  
Thumb Screw Adjustment

FLG3 Wire Grabber™

Patent pending


**Kits available**  
**Straight**  
**and "Y"**  
**with loop,**  
**toggles**  
**or hooks**

**Reliable hanging support of static loads up to 75 lbs.**

**Secure grip on wire**  
Tightening this screw engages six points of contact on wire

FLG3 Exploded view

**Easy to use**  
Push wire through connector and out the other side. Loop wire back through connector. Tighten screw.



Now it's easier than ever to get reliable hanging support for fixtures, fixture boxes, cable tray and other static loads requiring drop wire support!


Better than traditional wire-hanging methods, **Wire Grabber™** saves time and **costs much less than competitive products.**

Perfect for dry or wet locations, Wire Grabber's hold on braided wire is unaffected by oil or grease. It holds an angular load as well as any other static load, including high bay light fixtures.

There's no internal spring. Finger tightening the new thumb screw engages six points of contact for easy length adjustment without kinking or bending the wire.

- Tighten screw with pliers or screwdriver to finish – no special tool required
- Connector ships fully assembled
- **Also available** in straight or "Y" kits with 2mm (.080") braided wire in lengths from five to thirty feet, with loop, toggles or hooks

Rolls of braided support wire also sold separately (details on reverse)



View Video



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
**800/233.4717**  
**Fax 570/562.0646**  
**www.aifittings.com**

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION Wire Grabber™	UNIT/STD PKG	WIRE GRABBER CAPACITY (LBS)	WIRE DIMENSION (INCHES)	WIRE DESCRIPTION (TYPE of WIRE)
FLG3	01590	Wire hanger for static loads up to 75 lbs on .080" galvanized braided wire	50 per box	75 LBS	.080" (2 mm dia.)	Arlington's BW580
				50 LBS	.062" (1.6 mm dia.)	Arlington's BW562

# WIRE GRABBER™

## Straight and "Y" Kits, Bulk Support Wire

### WIRE GRABBER™ KIT • STRAIGHT • LOOPED END

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION Straight Kit	WIRE LENGTH	UNIT PKG	STD PKG
DWB0805	06805	Straight Kit	5'	1	10
DWB0812	06883	w/ Looped End holds static loads	10'	1	10
DWB0815	06815	up to 75 lbs	15'	1	10
DWB0820	06820	(w/ supplied	20'	1	10
DWB0830	06830	.080" wire)	30'	1	10

Straight Kits



Straight kits include FLG3 wire hanger, .080" galvanized braided wire – with loop, one toggle or one hook on the end.


### WIRE GRABBER™ KIT • STRAIGHT • TOGGLE ON END

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION Straight Kit	WIRE LENGTH	UNIT PKG	STD PKG
DWT0810	15021	Straight wire, (1) toggle on end	10'	1	10




### WIRE GRABBER™ KIT • STRAIGHT • HOOK ON END

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION Straight Kit	WIRE LENGTH	UNIT PKG	STD PKG
DWH0810	15023	Straight wire, (1) hook on end	10'	1	10



"Y" Kits

Includes FLG3 wire hanger, .080" galvanized braided wire – hooks on each end of the 18" Y.



Includes FLG3 wire hanger, .080" galvanized braided wire – toggles on each end of an 18" or 12" Y.

### WIRE GRABBER™ KIT • 18 INCH "Y" with HOOKS

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION "Y" Kit	WIRE LENGTH	UNIT PKG	STD PKG
DWYH0805	11307	"Y" Kit	5'	1	10
DWYH0810	11308	with Hooks	10'	1	10
DWY2H0810*	11312	holds static loads	10'	2	10
DWYH0815	11309	up to 75 lbs	15'	1	10
DWYH0820	11310	(w/ supplied	20'	1	10
DWYH0830	11311	.080" wire)	30'	1	10

\*2-pack has 150 lb rating


### WIRE GRABBER™ KIT • 18 INCH "Y" with TOGGLES

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION "Y" Kit	WIRE LENGTH	UNIT PKG	STD PKG
DWYT0805	11301	18" Y Kit	5'	1	10
DWYT0810	11302	with Toggles	10'	1	10
DWY2T0810*	11306	holds static loads	10'	2	10
DWYT0815	11303	up to 75 lbs	15'	1	10
DWYT0820	11304	(w/ supplied	20'	1	10
DWYT0830	11305	.080" wire)	30'	1	10

### WIRE GRABBER™ KIT • 12 INCH "Y" with TOGGLES

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION "Y" Kit	WIRE LENGTH	UNIT PKG	STD PKG
DWYT0812	11313	12" Y Kit	5'	1	10
DWY2T0812*	11314	with Toggles	5'	2	10

\*2-packs have 150 lb rating



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
www.aifittings.com

View Video



### GALVANIZED, BRAIDED SUPPORT WIRE • 500 FT ROLLS

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION Galvanized Support Wire	UNIT PKG	STD PKG
BW580	21250	Braided .080" (5/64")	1 roll	4 rolls/carton
BW562	83775	Braided .062" (1/8" dia.)	1 roll	4 rolls/carton

Distributed by