

Eaton E57LBL12T110SD

Premium+ Inductive Proximity Sensor, E57, 2 mm range, Straight, 12 mm, Shielded, 360° viewable LED, M12, 500 mA at 6-30 Vdc, 4 pin, <1% sensing range, NC PNP open collector, 6-48 Vdc

General specifications

PRODUCT NAME	Eaton E57 inductive proximity sensor
CATALOG NUMBER	E57LBL12T110SD
UPC	782113605098
PRODUCT LENGTH/DEPTH	2.71 in
PRODUCT HEIGHT	0.47 in
PRODUCT WIDTH	0.47 in
PRODUCT WEIGHT	0.1 lb
WARRANTY	1 year
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

TYPE	Premium+ Inductive Proximity Sensor
CONTACT RATING	500 mA at 6-30 Vdc
ACTUATOR FUNCTION	Shielded
ACCURACY	< 1% sensing range
ENCLOSURE MATERIAL	303 stainless steel
CONNECTION	M12
CONTACT CONFIGURATION	NC PNP open collector
SERIES	E57
ENVIRONMENTAL RATING	NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67, IP69K
NUMBER OF PINS	4
OPERATING TEMPERATURE - MAX	158 °F
OPERATING TEMPERATURE - MIN	-13 °F
MAXIMUM DC CURRENT	500 mA
INPUT VOLTAGE	6-48 Vdc
LED INDICATOR	360 ° viewable LED
PROTECTION	Auto reset

Resources

CATALOGS	Product Range Catalog Sensors – products, basic information, applications
MULTIMEDIA	We make what matters
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - E57LBL12T110SD

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.