



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E5830DP150GL Harsh-Duty 150MM 6 In Perfect Prox Ac/DC Cable

Eaton Corp

Catalog Number	E5830DP150GL
Manufacturer	Eaton Corp
Description	Eaton Harsh-Duty Sensor, Perfect Prox Photoelectric Sensor, E58, Through Beam, Straight, Output On, Flashes When Latched, 6.6 FT, 300 Ma At 20-132 Vac/15-30 VDC, PVC, Ac: L1 Switched, DC: NPN Open Collector, 20-132 Vac 50/60 HZ, 15-30 VDC
Weight per unit	0.4500 (lbs/each)
Product Category	Photoelectric Sensors

### Dimensions and Weight

Height	1.18
Length	4.36
Width	1.18

### Descriptions

Description	HARSH-DUTY 150MM 6 IN PERFECT PROX AC/DC CABLE
extra long description	ETN E58-30DP150-GL PHOTO SENSOR,HD,
Features	Eaton's E58 harsh-duty series sensors are among the most rugged and best-sealed photoelectric sensors. Stainless steel, PVDF and tempered glass components are mechanically assembled using Vitron seals to ensure resistance to chemicals and moisture intrusion. These sensors withstand heavy shock and vibration while providing unparalleled optical performance.
Long Description	Eaton harsh-duty sensor, Perfect Prox Photoelectric Sensor, E58, Through Beam, Straight, Output ON, flashes when latched, 6.6 ft, 300 mA at 20-132 Vac/15-30 Vdc, PVC, AC: L1 switched, DC: NPN open collector, 20-132 Vac 50/60 Hz, 15-30 Vdc
Product Type	Photo Sensor, HD, 6" Pprox, Acdc, LT, CBL

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113094298
Manufacturers Part Number	E58-30DP150-GL
UPC	782113094298

### Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Harsh-duty sensor

### Packaging

Carton	1
Weight Per each	0.45



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Vehicles: On-Road - PickUp & Delivery: Food .....
Operating Temperature .....	-40° to 131°F (-40° to 55°C) .....
standard .....	UL Listed .....