

Eaton ECP242408

Catalog Number: ECP242408

Eaton Crouse-Hinds series ECP enclosure, Square cover, 9-7/16" depth, 24" x 24" x 8", Copper-free aluminum, Tap-in mounting feet

General specifications




Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series ECP enclosure	ECP242408
	UPC
	662276321984
Product Length/Depth	Product Height
29.33 in	29.33 in
Product Width	Product Weight
12.53 in	279 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

3R

4

7

9

Product specifications

Enclosure size

24" x 24" x 8"

Cover type

Square

Depth

9-7/16 in

Material

Copper-free aluminum

Special features

Tap-in mounting feet

Resources

3D CAD drawing package

[Eaton Crouse-Hinds ECP242408 3D drawing](#)

Brochures

[Crouse-Hinds series ECP Enclosures Brochure](#)

Catalogs

[Crouse-Hinds series ECP catalog page](#)

Certification reports

[Intertek EC-Type Examination Certificate](#)

[ECP Explosionproof Enclosures UL certification](#)

[IECEX Certificate of Conformity](#)

Installation instructions

[IF 1107 - Mounting Plate Kit](#)

[IF 1639 - ECP Explosionproof Enclosures](#)

Specifications and datasheets

[ECP Enclosures](#)

[Eaton Specification Sheet - ECP242408](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)