



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EDSC271SA PB/P-Lite Station *Crouse-Hinds*

Catalog Number	EDSC271SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Flexstation Eds Back Box, Copper-Free Aluminum, Single-Gang, Through Feed, 3/4"
Weight per unit	2.5 (lbs/each)
Product Category	Control Station Enclosures

### Features

dimensions	5.0000 IN X 3.7000 IN X 8.2000 IN
Material	Copper-Free Aluminum

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Description	PB/P-LITE STATION
extra long description	CRS-H EDSC271 SA EDSC FLEX STATION
Features	Crouse-Hinds series FlexStation components are combined to provide a variety of control stations which are used in conjunction with magnetic starters or contactors for remote control of motors and other electrical apparatus. Used in petroleum refineries, chemical, petrochemical; grain processing and storage; heavy industrial applications where Class I, II, or III hazards are present.
Long Description	Eaton Crouse-Hinds series FlexStation EDS back box, Copper-free aluminum, Single-gang, Through feed, 3/4"
Product Type	Edsc Flex Station CNTRL Station

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274871158
Manufacturers Part Number	EDSC271 SA
UPC	782274871158

### Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION MOTOR CONTROL
Type	BACK BOX

### Packaging

Carton	1
Weight Per each	2.45



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
Enclosure	CLASS I DIV 1 AND 2 GROUP B C D, CLASS II DIV 1 GROUP E F G, CLASS II DIV 2 GROUP F G, CLASS III, NEMA 3/7B/7C/7D/9E/9F/9G