



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EN2850 28" Enclosure W/Hinged Cover + Lock

Pass & Seymour/Legrand

Catalog Number	EN2850
Manufacturer	Pass & Seymour/Legrand
Description	<P>This 28"" Enclosure Is The Perfect Solution For A Basic Structured Wiring System. It Features Larger Top Openings That Make Pulling Wire Easier As Well As Additional Knockouts, More Side Lances, and Side Tabs For More Flexible Mounting. It Includes A H
Weight per unit	16.3 (lbs/each)
Product Category	Enclosures & Cabinets

Features

Cable Entry	(2) rectangular knockouts for 1-gang electrical box
Enclosure Size	28.0
face plate	Hinged Cover and Lock
frame	Cold Rolled Steel
Material	Steel

Material, Color, and Finish

Color	White
Finish	Powder Coat

Dimensions and Weight

Depth	3.7"
Height	28.1"
Thickness	0.1
Width	14.3"

Descriptions

Description	28" ENCLOSURE W/HINGED COVER + LOCK
extra long description	OnQ EN2850 28 ENCL W/HINGED COVER +
Long Description	<p>This 28"" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a h
Product Type	28 Encl W/Hinged Cover + Lock
Special Features	Flanged covers hide drywall openings- Flush and surface-mounted- Mounting tabs provide correct flush-mount position



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428023135
Manufacturers Part Number	EN2850
UPC	804428023135

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	ENCLOSURE

Packaging

Carton	1
Weight Per each	16.25

Uses, Certifications, and Standards

Application	Residential
Mounting	Surface or Flush
standard	ROHS, CSA, UL, CULUS, UL (UL985, UL1023, UL1863), cULus, CSA, RoHS