



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESX1LEDP450KR5MV *Delisted* ESX1 Led P4 50K R5 Mvolt Upa BLS DDBXD *Lithonia Lighting - Acuity*

Catalog Number	ESX1LEDP450KR5MV
Manufacturer	Lithonia Lighting - Acuity
Description	Lith ESX1 Led P4 50K R5 Mvolt Upa B
Weight per unit	11.7 (lbs/each)
Product Category	Lighting

Features

average life	60,000
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	21,000 LM,22,000 LM,23,000 LM,24,000 LM,25,000 LM
Material	Aluminum
Maximum Operating Temperature	40
media	Yes
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Wattage	200

Material, Color, and Finish

Color	Bronze
color rendering index (cri)	70
color temperature	5000
Finish	Gloss
Lens Color	Clear
Lens Material	Glass
Style	CONTEMPORARY

Dimensions and Weight

Height	2.87
Length	19.94
Width	12

Descriptions

Description	*DELISTED* ESX1 LED P4 50K R5 MVOLT UPA BLS DDBXD
Long Description	LITH ESX1 LED P4 50K R5 MVOLT UPA B
Product Type	Area Light



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194994838548
Manufacturers Part Number	ESX1 LED P4 50K R5 MVOLT UPA B
UPC	194994838548

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	2
Weight Per each	11.73

Uses, Certifications, and Standards

Application	Automotive & Parking, Offices & Banks, Retail
environmental conditions	OUTDOOR
Mounting	Arm Mount, Surface
standard	C-UL-USDLC Premium, Nighttime Friendly