



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV1410FBQ 16-14AWG #10STD Blue Fork TRML *Panduit Corporation*

Catalog Number	EV1410FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV14-10FB-Q Contractor Grade Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Fork Design Provides For Fast and Easy Installation, Without The Need to Remove Fastener. Accommodates 16-14 Awg, Compatible With #10 Stud (M5), Are Blue In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
insulation	Vinyl
Material	Copper
media	Yes
Wire Size	#14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	16-14AWG #10STD BLUE FORK TRML
extra long description	PAN EV14-10FB-Q StrongHold™ EV14-10
Long Description	StrongHold EV14-10FB-Q Contractor Grade Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The fork design provides for fast and easy installation, without the need to remove fastener. Accommodates 16-14 AWG, compatible with #10 Stud (M5), are blue in color, and come in packages of 25.
Product Type	Stronghold™ EV14-10FB-Q Loose Piece Forks, Blue, Vinyl, 1/5"

Manufacturer Information

Brand	Panduit®
GTIN	00613056366435
Manufacturers Part Number	EV14-10FB-Q
UPC	613056366435



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Fork Terminal

Packaging

Carton 25

Package 250

Weight Per each 0.05

Uses, Certifications, and Standards

Mounting 0.31

standard UL Listed 587H E52164; CSA Certified LR31212