



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EWZ120 Astro 277 Clock

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | EWZ120  |
| Manufacturer     | Nsi Industries  |
| Description      | The Tork EWZ120 7-Day Astronomic Digital Timer Is Designed For 30 Amp / 120-277 Volt Loads and Has A Noryl Plastic Enclosure With A Locking Hasp For Outdoor Use. Automate Your Home or Office to Save Energy and Money Using The Intuitive Programming Interface to Activate Lights or Signage. Features One SPDT Output Channel With Automatic Voltage Detection. Designed For Commercial Applications Including Outdoor Lighting, Motors, Security or Parking Lot Lights, and Heating or Air Conditioning Equipment. |
| Weight per unit  | 2.0 (lbs/each)  |
| Product Category | Electronic Time Switches  |

### Features

|                |              |
|----------------|--------------|
| action         | SPDT         |
| Base           | Screw        |
| Contact Rating | 120-277 VAC  |
| Phase          | Single Phase |
| Poles          | 1            |
| Timing Range   | 7 DAY        |

### Dimensions and Weight

|      |                             |
|------|-----------------------------|
| Size | L=5.062 - H=8.312 - W=3.062 |
|------|-----------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | ASTRO 277 CLOCK   |
| extra long description | TORK EWZ120 Astro Digital Timer SPD   |
| Features               | Digital timers simplify your life by automating repeating parts of your schedule, saving the user time, energy and money. The EWZ120 is a 7-day astronomic lighting control timer, ideal for applications in the home, office, factory, church or school. Use a photocell sensor to detect when the ambient light level drops below a programmable threshold, then turn on everything from signage to meeting room lights. Program in up to 20 different on/off settings with unique schedules for each day of the week using t |
| Long Description       | The TORK EWZ120 7-Day Astronomic Digital Timer is designed for 30 amp / 120-277 volt loads and has a Noryl plastic enclosure with a locking hasp for outdoor use. Automate your home or office to save energy and money using the intuitive programming interface to activate lights or signage. Features one SPDT output channel with automatic voltage detection. Designed for commercial applications including outdoor lighting, motors, security or parking lot lights, and heating or air conditioning equipment.         |
| Product Type           | Astro Digital Timer SPDT  |
| Special Features       | 20 On-Off Set Points - Daylight Savings Auto - Leap Year Automatic Compensation   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00786261824714 |
| Manufacturers Part Number | EWZ120         |
| UPC                       | 786261824714   |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Fuses & Fuse Accessories                      |
| Type                 | 7 Day Astronomic Time Switch - 1 Or 2 Channel |

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 2 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | NSI  |
| Enclosure                | NEMA 3R Plastic Indoor-Outdoor With Locking Hasp |
| environmental conditions | -40 to + 149 F                                   |
| Frequency Rating         | 50-60 Hz   |
| Mounting                 | Screw Mount                                      |
| Operating Temperature    | -40 to + 149 F                                   |
| standard                 | cULus  |