



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EYS86SA 3" Alu Cond Seal *Crouse-Hinds*

Catalog Number	EYS86SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eys Conduit Sealing Fitting, Male and Female, Copper-Free Aluminum, Vertical or Horizontal, 3"
Weight per unit	5.0 (lbs/each)
Product Category	Aluminum

Features

connection	Male Threaded, Female Threaded
dimensions	4.2500 IN X 4.2500 IN X 8.5000 IN

Descriptions

Description	3" ALU COND SEAL
extra long description	CRS-H EYS86 SA 3 NPT MALE/FEM AL VE
Features	Crouse-Hinds series EYS and EZS explosionproof sealing fittings restrict the passage of gases, vapors or flames from one portion of the electrical installation to another, limit explosions to the sealed off enclosure, and limit pre-compression or "pressure piling" in conduit systems. EYS sealing fittings are available for installation in either vertical only or in both horizontal or vertical positions. They are available in a variety of materials, including Feraloy iron alloy and/or ductile iron, copper-
Long Description	Eaton Crouse-Hinds series EYS conduit sealing fitting, Male and female, Copper-free aluminum, Vertical or horizontal, 3"
Product Type	3 NPT Male/Fem Al Vert/Horz Seal FTG
Special Features	Horizontal/Vertical Position

Manufacturer Information

Brand	Eaton
GTIN	00782274379814
Manufacturers Part Number	EYS86 SA
UPC	782274379814

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Conduit sealing fitting

Packaging

Carton	1
Weight Per each	5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	CLASS I DIV 1 2 GROUP C D, CLASS II DIV 1 2 GROUP E F G, CLASS III
standard	UL 886, CSA C22.2