



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EZT2090S Ez Trim Surface Unvented For 20"W X 90"H Box Wem2 *Eaton Corp*

Catalog Number	EZT2090S
Manufacturer	Eaton Corp
Description	Eaton Pow-R-Xpress Ez Trim Surface Unvented For 20"W X 90"H Box WEM2 Keyed
Weight per unit	370.0 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	78.0000 IN X 20.0000 IN X 2.0000 IN
Material	Copper
media	Yes

Descriptions

Description	EZ TRIM SURFACE UNVENTED FOR 20"W X 90"H BOX WEM2
extra long description	ETN EZT2090S EZ TRIM,S,UNVENT 20WX9
Features	The Pow-R-Xpress program brings to you a new set of products - Pow-R-Xpress panelboards. The Pow-R-Xpress products include interiors; type 1 and 3R boxes; surface and flush trims; main breaker kits; branch breakers; lug kits; service entrance kits; ground kits; and 200% neutral kits. In addition, the distributor stocking program can be used with various Eaton commercial distribution products and is designed to meet UL67 standards for use in data center, industrial, commercial and healthcare facilities.
Long Description	Eaton Pow-R-Xpress EZ trim surface unvented for 20"W X 90"H box WEM2 Keyed
Product Type	Ez Trim, S, Unvent 20WX90H WEM2 Keyed
Special Features	Pow-R-Xpress

Manufacturer Information

Brand	Eaton
GTIN	00786685355412
Manufacturers Part Number	EZT2090S
UPC	786685355412

Taxonomies, Classifications, and Categories

Category Description	Panelboard Boxes, Covers, Latches, Directories
Type	Accessory

Packaging

Carton	1
Weight Per each	370



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - OtherElec Assemblies, Panels & OEM - Electrical
Assemblies, Panels and OEMs

standard

UL 67