



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F017835ECO 17W T8 24" 3500K 82 Cri Bi-Pin *Sylvania-Ledvance*

Catalog Number	F017835ECO
Manufacturer	Sylvania-Ledvance
Description	17W, 24" Mol, T8 Octron Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 82 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.2400 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	17

Material, Color, and Finish

color rendering index (cri)	82
Finish	Phosphor Coated

Descriptions

Description	17W T8 24" 3500K 82 CRI BI-PIN
extra long description	SYL FO17835ECO/22136 FO17835ECO 30/
Long Description	17W, 24" MOL, T8 OCTRON fluorescent lamp, 3500K color temperature, rare earth phosphor, 82 CRI, suitable for IS or RS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221361
Manufacturers Part Number	FO17/835/ECO/22136
UPC	046135221361

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.24