Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy
30165-0000, GA Rome
Phone: 706-622-4953
Fax: 706-622-4954



F025841EC0 25W T8 36" 4100K 2150LM

Sylvania-Ledvance

Catalog Number	F025841EC0
Manufacturer	Sylvania-Ledvance
Description	25W, 36" Mol, T8 Octron Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 82 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.3300 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	25

Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Finish	Phosphor Coated

Descriptions

Description	25W T8 36" 4100K 2150LM
extra long description	LDV FO25841ECO/22140 FO25841ECO 30/
Long Description	25W, 36" MOL, T8 OCTRON fluorescent lamp, 4100K color temperature, rare earth phosphor, 82 CRI, suitable for IS or RS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221408
Manufacturers Part Number	FO25/841/ECO/22140
UPC	046135221408

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.33