



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F032835ECO 32W T8 48" 3500K 82 Cri Bi-Pin Energy Saving *Sylvania-Ledvance*

Catalog Number	F032835ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48" Mol, T8 Octron Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.4200 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	85
Finish	Phosphor Coated

Descriptions

Description	32W T8 48" 3500K 82 CRI BI-PIN ENERGY SAVING
extra long description	SYL FO32835ECO/21779 FO32835ECO 30/
Long Description	32W, 48" MOL, T8 OCTRON fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, suitable for IS or RS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135217791
Manufacturers Part Number	FO32/835/ECO/21779
UPC	046135217791

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	30
Weight Per each	0.42

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------