



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F096850ECO 59W T8 96" 5000K 80 Cri Single Pin Energy Saving

*Sylvania-Ledvance*

Catalog Number	F096850ECO
Manufacturer	Sylvania-Ledvance
Description	59W, 96" Mol, T8 Octron Fluorescent Lamp, 5000K Color Temperature, Rare Earth Phosphor, 80 Cri, Suitable For Is Operation, Ecologic
Weight per unit	0.9200 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	15000
Base	Single Pin
bulb type	T8
Lamp Type	INSTANT START
lumens	5900
Shape	T8
start type	Instant Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	59

### Material, Color, and Finish

color rendering index (cri)	80
color temperature	5000
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1
Length	94

### Descriptions

Description	59W T8 96" 5000K 80 CRI SINGLE PIN ENERGY SAVING
extra long description	SYL FO96850ECO/22173 FO96850ECO 24/
Long Description	59W, 96" MOL, T8 OCTRON fluorescent lamp, 5000K color temperature, rare earth phosphor, 80 CRI, suitable for IS operation, ECOLOGIC
Product Type	FO96850ECO 24/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221736
Manufacturers Part Number	FO96/850/ECO/22173
UPC	046135221736



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

## Packaging

Carton 1

Package 24

Weight Per each 0.92

## Uses, Certifications, and Standards

Application Commercial/Residential