

**Product Number:** 21409

**Order Abbreviation:** F14T12/CW

**General Description:** 14W T12 preheat fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI. 9000 Avg rated life at 3 hrs/start



**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	F14T12CW 30/CS 1/SKU
Actual Length (in)	14.780
Actual Length (mm)	375.41
Average Rated Life (hr)	9000
Base	Medium Bipin
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.591
Diameter (mm)	40.40
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	650
Mean Lumens at 25C	566
Nominal Length (in)	15.000
Nominal Length (mm)	381.00
Nominal Wattage (W)	14.00

#### Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.