Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F15T8CW 15W T8 18" Cool White 62 Cri Bi-Pin Fluor Lamp

Sylvania-Ledvance

Catalog Number	F15T8CW
Manufacturer	Sylvania-Ledvance
Description	15W T8 Preheat Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri. 7500 Avg Rated Life At 3 HRS/Start
Weight per unit	0.1900 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	PREHEAT
lumens	825 Initial Lumens at 25 Degrees C
Shape	T8
start type	PREHEAT
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

Descriptions

Description	15W T8 18" COOL WHITE 62 CRI BI-PIN FLUOR LAMP
extra long description	LDV F15T8CW/21616 F15T8CW 24/CS 1/S
Long Description	15W T8 preheat fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI. 7500 Avg rated life at 3 hrs/start
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135216169
Manufacturers Part Number	F15T8/CW/21616
UPC	046135216169

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	24
Weight Per each	0.19

Uses, Certifications, and Standards

Application	Commercial/Residential