



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F40T8SPX41 *Delisted* 40W T8 60" 41K Med Bi-Pin 84 Cri Fluor

Ge By Current Lamps

Catalog Number	F40T8SPX41
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Medium Bi-Pin (G13) Base, T8 Bulb Shape, 84, 20000 H Average Life, 4100 K, 40 W, 3725 LM Brightness (Lumens), Soda Lime Housing Material, 1.0 In Diameter, 60 In Length, Rapid, +10 °C Operating Temperature, 0.654 LB/Ea
Weight per unit	0.6540 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	3725.0
Wattage	40.0

Material, Color, and Finish

color rendering index (cri)	84.0
-----------------------------	------

Descriptions

Description	*DELISTED* 40W T8 60" 41K MED BI-PIN 84 CRI FLUOR
-------------	---

Manufacturer Information

Brand	GE Current
GTIN	00043168226622
Manufacturers Part Number	F40T8/SPX41
UPC	043168226622

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	24
Weight Per each	0.654