



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F48T12CWHO 60W T12 48" Cool White High Output 62 Cri R17D

Sylvania-Ledvance

Catalog Number	F48T12CWHO
Manufacturer	Sylvania-Ledvance
Description	60W, 48" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri.
Weight per unit	0.6800 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
bulb type	T12
Lamp Type	RAPID START
lumens	4,050
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	60

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

Descriptions

Description	60W T12 48" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	SYL F48T12CWHO/25146 F48T12CWHO 30/
Long Description	60W, 48" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI.
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251467
Manufacturers Part Number	F48T12/CW/HO/25146
UPC	046135251467

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.68



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application Commercial/Residential