



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F60T12DH015 75W T12 60" Daylight High Output 76 Cri R17D

*Sylvania-Ledvance*

Catalog Number	F60T12DH015
Manufacturer	Sylvania-Ledvance
Description	75W, 60" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylight Phosphor, 6500K Color Temperature, 72 Cri
Weight per unit	0.8600 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

bulb type	T12
-----------	-----

### Descriptions

Description	75W T12 60" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	SYL F60T12/D/HO/22512 F60T12DHO 15/
Long Description	75W, 60"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylight phosphor, 6500K color temperature, 72 CRI
Product Type	F60T12DHO 15/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135225123
Manufacturers Part Number	F60T12/D/HO/22512
UPC	046135225123

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	15
Weight Per each	0.86