



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196



F96T12CWH0CT 110W T12 96" Cool White Cold Temp Ho 62 Cri R17D

Ge By Current Lamps

Catalog Number	F96T12CWH0CT
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, R17D Recessed Double Contact Base, T12 Bulb Shape, 60, 12000 H Average Life, 4100 K, Cool White, 800 Ma, 110 W, 3710 LM Brightness (Lumens), Soda Lime Housing Material, Shatter Resistant Coated, 1.5 In Diameter, 48.0 In Length, Instant;Rapid, 1.3 LB/Ea
Weight per unit	1.3 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Recessed Double Contact (R17d)
lumens	8900
Wattage	110

Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
----------	-----

Descriptions

Description	110W T12 96" COOL WHITE COLD TEMP HO 62 CRI R17D
extra long description	GEL F96T12/CW/HO/CT 11918 FLUORESCE

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168119184
UPC	043168119184

Taxonomies, Classifications, and Categories

Category Description	HIGH VOLUME FLUORESCENTS
----------------------	--------------------------

Packaging

Carton	1
Package	15
Weight Per each	1.32