

# Fluorescent Lamps



Bulb	Base	Nominal Length Watts in.	Order Code	Description	Case Qty.	Rated Life (hours)	Lumens Initial	Lumens Mean	Color Temp. K	CRI	Footnotes	Warning and Cautions	Additional Information
<b>T8 STARCOAT® LAMPS (CONTINUED)</b>													
<b>T8 MOD-U-LINE®</b>													
<b>T8 1 5/8" SPACING</b>													
T8	Medium BiPin (G13)	31	22.5	41776 F31T8/SPX30/U	15	20000	2725	2500	3000	82	Ⓢ		105
				41777 F31T8/SPX35/U	15	20000	2725	2500	3500	82	Ⓢ		105
				41778 F31T8/SPX41/U	15	20000	2725	2500	4100	82	Ⓢ		105
<b>T8 6" SPACING</b>													
T8	Medium BiPin (G13)	32	22.5	10479 F32T8/SP30/U/6	12	20000	2700	2565	3000	78	Ⓢ		105
				23585 F32T8/SP35/U/6	12	20000	2700	2565	3500	78	Ⓢ		105
				10480 F32T8/SP41/U/6	12	20000	2700	2565	4100	78	Ⓢ		105
				10483 F32T8/SPX30/U/6	12	20000	2800	2630	3000	86	Ⓢ		105
				10485 F32T8/SPX35/U/6	12	20000	2800	2630	3500	86	Ⓢ		105
				10488 F32T8/SPX41/U/6	12	20000	2800	2630	4100	86	Ⓢ		105
				10489 F32T8/SPX50/U/6	12	20000	2660	2510	5000	86	Ⓢ		105
<b>F25T12 FOR T8 BALLASTS</b>													
T12	Medium BiPin (G13)	25	48	11439 F25T12/SP30	30	15000	2300	2140	3000	70	Ⓢ	➔	101
				11440 F25T12/SP35	30	15000	2300	2140	3500	70	Ⓢ	➔	101
				11442 F25T12/SP41	30	15000	2300	2140	4100	70	Ⓢ	➔	101
<b>8' T8 LAMPS</b>													
<b>8' T8</b>													
T8	Single Pin (Fa8)	59	96	23407 F96T8/SP30	24	15000	5800	5500	3000	78	Ⓢ		101
				23411 F96T8/SP35	24	15000	5800	5500	3500	78	Ⓢ		101
				23412 F96T8/SP41	24	15000	5800	5500	4100	78	Ⓢ		101
				23414 F96T8/SPX30	24	15000	5950	5650	3000	86	Ⓢ		101
				23415 F96T8/SPX35	24	15000	5950	5650	3500	86	Ⓢ		101
				23416 F96T8/SPX41	24	15000	5950	5650	4100	86	Ⓢ		101
				23575 F96T8/SPX50	24	15000	5950	5650	5000	86	Ⓢ		101
<b>8' T8 XL EXTRA-LIFE</b>													
T8	Single Pin (Fa8)	59	96	41889 F96T8/XL/SP30	24	18000	5800	5500	3000	78	Ⓢ		101
				41890 F96T8/XL/SP35	24	18000	5800	5500	3500	78	Ⓢ		101
				41891 F96T8/XL/SP41	24	18000	5800	5500	4100	78	Ⓢ		101
				41892 F96T8/XL/SPX30	24	18000	5950	5650	3000	86	Ⓢ		101
				41893 F96T8/XL/SPX35	24	18000	5950	5650	3500	86	Ⓢ		101
				41894 F96T8/XL/SPX41	24	18000	5950	5650	4100	86	Ⓢ		101
				45497 F96T8/XL/SPX50	24	18000	5950	5650	5000	86	Ⓢ		101
<b>WATT-MISER® ENERGY SAVING LAMPS</b>													
<b>8' T8 WATT-MISER® XL EXTRA-LIFE</b>													
T8	Single Pin (Fa8)	57	96	48524 F96T8/XL/SP30/WM	24	18000	5800	5450	3000	84	Ⓢ	➔	101
				48525 F96T8/XL/SP35/WM	24	18000	5800	5450	3500	83	Ⓢ	➔	101
				48526 F96T8/XL/SP41/WM	24	18000	5800	5450	4100	81	Ⓢ	➔	101
<b>8' T8 HIGH OUTPUT</b>													
<b>8' T8 HIGH OUTPUT - RECESSED DOUBLE CONTACT</b>													
T8	R17d	86	96	12536 F96T8/SP30/HO	24	18000	8000	7600	3000	78	Ⓢ		101
				12537 F96T8/SP35/HO	24	18000	8000	7600	3500	78	Ⓢ		101
				12538 F96T8/SP41/HO	24	18000	8000	7600	4100	78	Ⓢ		101
				12533 F96T8/SPX35/HO	24	18000	8200	7800	3500	86	Ⓢ		101
				12534 F96T8/SPX41/HO	24	18000	8200	7800	4100	86	Ⓢ		101
				12535 F96T8/SPX50/HO	24	18000	8200	7800	5000	86	Ⓢ		101

Ⓢ Means this lamp meets Federal Minimum Efficiency Standards.