




GE
Lighting

28106 - F96T8/SP35/ECO

GE Ecolux® T8

- Passes TCLP, which can lower disposal costs.



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Single Pin (Fa8)
Rated Life	15000.0 hrs
Rated Life (instant start) @ Time	15000 h @ 3 h 20000 h @ 12 h
Bulb Material	Soda lime
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	123 picograms Hg per mean lumen hour
Additional Info	TCLP compliant
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	5700.0
Mean Lumens	5130.0
Nominal Initial Lumens per Watt	96
Color Temperature	3500.0 K
Color Rendering Index (CRI)	75.0

ELECTRICAL CHARACTERISTICS

Wattage	59.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	96.0000 in(2438.4 mm)
Nominal Length	96.000 in(2438.4 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	28106
Description	F96T8/SP35/ECO
Standard Package	Case
Standard Package GTIN	10043168281062
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168281065




GE
Lighting

28106 - F96T8/SP35/ECO

GE Ecolux® T8

- Passes TCLP, which can lower disposal costs.



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Single Pin (Fa8)
Rated Life	15000.0 hrs
Rated Life (instant start) @	15000 h @ 3 h
Time	20000 h @ 12 h
Bulb Material	Soda lime
Starting Temperature (MIN)	10.0 °C
LEED-EB MR Credit	123 picograms Hg per mean lumen hour
Additional Info	TCLP compliant
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	5700.0
Mean Lumens	5130.0
Nominal Initial Lumens per Watt	96
Color Temperature	3500.0 K
Color Rendering Index (CRI)	75.0

ELECTRICAL CHARACTERISTICS

Wattage	59.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	96.0000 in(2438.4 mm)
Nominal Length	96.000 in(2438.4 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	28106
Description	F96T8/SP35/ECO
Standard Package	Case
Standard Package GTIN	10043168281062
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168281065