ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

FB0328356EC0 32W T8 22.5" 35K 82CRI 6" Leg Space Is or RS Op

Sylvania-Ledvance

Catalog Number	FB0328356EC0
Manufacturer	Sylvania-Ledvance
Description	32W, 22.5" Mol, T8 Octron Curvalume Fluorescent Lamp, 6" Leg Spacing, 3500K Color Temperature, Rare Earth Phoshor, 82 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.6200 (lbs/each)
Product Category	Shape Lamps

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	82

Descriptions

Description	32W T8 22.5" 35K 82CRI 6" LEG SPACE IS OR RS OP
extra long description	LDV FBO32/835/6/ECO/21670 FBO328356
Long Description	32W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 6" leg spacing, 3500K color temperature, rare earth phoshor, 82 CRI, suitable for IS or RS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135216701
Manufacturers Part Number	FBO32/835/6/ECO/21670
UPC	046135216701

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	16
Weight Per each	0.62