



## FDI10250Q Highland Nylon Ins Female Disconnect, 12-10awg

*Minnesota Mining (3M)*

Catalog Number	FDI10250Q
Manufacturer	Minnesota Mining (3M)
Description	3M™ Highland™ Color-Coded Female Disconnect Terminal Has Dents and Rolled Edges to Offer Superior Holding Force While Allowing For Quick and Easy Disconnect. The Terminal Has A Fully Insulated, Nylon, Butted-Seam Barrel and Withstands Temperatures Of -40 to 221 Degrees F (-40 to 105 Degrees C). Its Durable Brass Construction Offers Good Conductivity and A Tin-Plated Finish Resists Corrosion.
Weight per unit	0.1250 (lbs/each)
Product Category	Small Terminals & Connectors

### Descriptions

Description	HIGHLAND NYLON INS FEMALE DISCONNECT, 12-10AWG
extra long description	3M 7000133657 3M™ Highland™ Nylon F
Features	3M™ Highland™ Color-Coded Female Disconnect Terminal attaches to the mating part with a tongue that slips over the male tab. The butted-seam barrel of this terminal provides electrical contact after crimping. The flared nylon sleeve is abrasion-resistant and fully insulated with a stepped design to ensure mistake-proof crimping. RoHS 2011/65/EU Compliant.
Long Description	3M™ Highland™ Color-Coded Female Disconnect Terminal has dents and rolled edges to offer superior holding force while allowing for quick and easy disconnect. The terminal has a fully insulated, nylon, butted-seam barrel and withstands temperatures of -40 to 221 degrees F (-40 to 105 degrees C). Its durable brass construction offers good conductivity and a tin-plated finish resists corrosion.
Product Type	3M™ Highland™ Nylon Fully Insulated Butted Seam Female Disco

### Manufacturer Information

Brand	Scotchlok
GTIN	00051128599990
Manufacturers Part Number	FDI10250Q
UPC	051128599990

### Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.125

## Uses, Certifications, and Standards

standard	UL and CSA
----------	------------