



GE
Lighting

61279 - FLE13HT3/2/827

FLE13HT3/2/827

Product Photo



GENERAL CHARACTERISTICS

Base Type	Screw-In
Bulb Material	Soft glass
Rated Life Hours-nominal	10000 h
Base Description	Medium Screw
Primary Application	Standard <General Purpose>
Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	T4

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	64
Initial Lumens-nominal	825.5 lm
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	61279
Description	FLE13HT3/2/827
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	0.37 in
Bulb Max Overall Length-MOL	4.8 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	60 W
Rated power (Watts)	13 W