




GE
Lighting

89632 - FLE15/2/A19XL

GE A19

 High Color Rendering
cUL Listed
Energy Savings



GENERAL CHARACTERISTICS

| | |
|---------------------------------------|--------------------------------------|
| Lamp Type | Compact Fluorescent - Self-Ballasted |
| Bulb | A19 |
| Base | Medium Screw (E26) |
| Bulb Finish | Soft white |
| Equivalent Wattage (NOM) | 60.0 W |
| Rated Life (NOM) | 10000.0 h |
| Starting Temperature (MIN) | 5.0 °C |
| Total Harmonic Distortion (THD) (NOM) | 120.0 % |
| Mercury Content (NOM) | 3.5 mg |
| Picograms of Mercury (NOM) | 530.3 pg |
| Primary Application | Standard |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------------|----------|
| Initial Lumens (NOM) | 825.0 |
| Mean Lumens (NOM) | 660.0 |
| Nominal Initial Lumens per Watt (NOM) | 55.0 |
| Color Temperature (NOM) | 2700.0 K |
| Color Rendering Index (CRI) (NOM) | 82.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|---------|
| Wattage (NOM) | 15.0 |
| Voltage (NOM) | 120.0 |
| Input Voltage (NOM) | 120.0 V |
| Input Current (NOM) | 0.17 A |
| Power Factor (NOM) | 0.6 |

DIMENSIONS

| | |
|------------------------------------|--------------------|
| Maximum Overall Length (MOL) (NOM) | 4.600 in(116.8 mm) |
| Nominal Length (NOM) | 4.600 in(116.8 mm) |
| Bulb Diameter (DIA) (NOM) | 2.375 in(60.3 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 89632 |
| Description | FLE15/2/A19XL |
| Standard Package | Case |
| Standard Package GTIN | 10043168896327 |
| Standard Package Quantity | 10 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 10 |
| UPC | 043168896320 |




GE
Lighting

89632 - FLE15/2/A19XL

GE A19



High Color Rendering
cUL Listed
Energy Savings



GENERAL CHARACTERISTICS

| | |
|---------------------------------------|--------------------------------------|
| Lamp Type | Compact Fluorescent - Self-Ballasted |
| Bulb | A19 |
| Base | Medium Screw (E26) |
| Bulb Finish | Soft white |
| Equivalent Wattage (NOM) | 60.0 W |
| Rated Life (NOM) | 10000.0 h |
| Starting Temperature (MIN) | 5.0 °C |
| Total Harmonic Distortion (THD) (NOM) | 120.0 % |
| Mercury Content (NOM) | 3.5 mg |
| Picograms of Mercury (NOM) | 530.3 pg |
| Primary Application | Standard |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------------|----------|
| Initial Lumens (NOM) | 825.0 |
| Mean Lumens (NOM) | 660.0 |
| Nominal Initial Lumens per Watt (NOM) | 55.0 |
| Color Temperature (NOM) | 2700.0 K |
| Color Rendering Index (CRI) (NOM) | 82.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|---------|
| Wattage (NOM) | 15.0 |
| Voltage (NOM) | 120.0 |
| Input Voltage (NOM) | 120.0 V |
| Input Current (NOM) | 0.17 A |
| Power Factor (NOM) | 0.6 |

DIMENSIONS

| | |
|------------------------------------|--------------------|
| Maximum Overall Length (MOL) (NOM) | 4.600 in(116.8 mm) |
| Nominal Length (NOM) | 4.600 in(116.8 mm) |
| Bulb Diameter (DIA) (NOM) | 2.375 in(60.3 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 89632 |
| Description | FLE15/2/A19XL |
| Standard Package | Case |
| Standard Package GTIN | 10043168896327 |
| Standard Package Quantity | 10 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 10 |
| UPC | 043168896320 |