



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FS100NJ 100 Va Enc CTRL XFRMR 277V-120V *Hammond Power Solutions*

Catalog Number	FS100NJ
Manufacturer	Hammond Power Solutions
Description	General Purpose Enclosed Control Transformer, 277 PV, 120 SV, 100 Va
Weight per unit	5.0 (lbs/each)
Product Category	20250326101053

Features

Wattage	100
---------	-----

Dimensions and Weight

Height	3.6
Length	3.09
Width	6.1

Descriptions

Description	100 VA ENC CTRL XFRMR 277V-120V
extra long description	HMND FS100NJ FUSION 100VA 277-120
Long Description	General Purpose Enclosed Control Transformer, 277 PV, 120 SV, 100 VA
Product Type	Fusion 100VA 277-120
Special Features	An indoor enclosed control transformer for easy surface mounting.

Manufacturer Information

Brand	Hammond Power Solutions
GTIN	00803423107901
Manufacturers Part Number	FS100NJ
UPC	803423107901

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Ecnlosed

Packaging

Carton	1
Weight Per each	5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	HVAC applications, signal ad alarm systems and motor control circuits.
Enclosure	FS-N1 - Indoor
Frequency Rating	50/60
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum