



**Southwire™**

TOOLS & EQUIPMENT

**SIMpull™ NON-CONDUCTIVE  
FISH TAPE**

## **SIMpull™ NON-CONDUCTIVE FISH TAPE**

**FTSP45-75NCT**  
**FTSP45-125NCT**  
**FTSP3-100NCT**  
**FTSP3-240NCT**



**Does not break  
when folded**



**Weighs less  
than steel**



**Does not  
rust**



**Faster install  
time**



**Glow in  
the dark**



**Non-conductive  
leader**

# SIMpull™ NON-CONDUCTIVE FISH TAPE

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape through EMT or PVC conduit\*
- Non-conductive, glow-in-the-dark, leader allows for easy install over existing wires
- Allows the fish tape to glide through conduit without binding at joints, couplings or 90 degree bends
- Combines the strength of a steel fish tape with greater flexibility than fiberglass fish tapes\*

**FTSP45-75NCT**  
**FTSP45-125NCT**  
**FTSP3-100NCT**  
**FTSP3-240NCT**



Model #	Stock #	Description	Length
FTSP45-75NCT	63029801	SIMpull™ Fish Tape 4.5mm 75' Non-Conductive Tip, Large Case	75ft/22.8M
FTSP45-125NCT	63163701	SIMpull™ Fish Tape 4.5mm 125' Non-Conductive Tip, Large Case	125ft/38.1M
FTSP3-100NCT	63029901	SIMpull™ Fish Tape 3mm 100' Non-Conductive Tip, Medium Case	100ft/30.4M
FTSP3-240NCT	63029701	SIMpull™ Fish Tape 3mm 240' Non-Conductive Tip, Large Case	240ft/73.1M

\* When compared to Southwire™ Steel and Fiberglass fish tapes



**Southwire™**

TOOLS & EQUIPMENT

**SIMpull™ NON-CONDUCTIVE  
FISH TAPE**

## **SIMpull™ NON-CONDUCTIVE FISH TAPE**

**FTSP45-75NCT**  
**FTSP45-125NCT**  
**FTSP3-100NCT**  
**FTSP3-240NCT**



**Does not break  
when folded**



**Weighs less  
than steel**



**Does not  
rust**



**Faster install  
time**



**Glow in  
the dark**



**Non-conductive  
leader**

# SIMpull™ NON-CONDUCTIVE FISH TAPE

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape through EMT or PVC conduit\*
- Non-conductive, glow-in-the-dark, leader allows for easy install over existing wires
- Allows the fish tape to glide through conduit without binding at joints, couplings or 90 degree bends
- Combines the strength of a steel fish tape with greater flexibility than fiberglass fish tapes\*

**FTSP45-75NCT**  
**FTSP45-125NCT**  
**FTSP3-100NCT**  
**FTSP3-240NCT**



Model #	Stock #	Description	Length
FTSP45-75NCT	63029801	SIMpull™ Fish Tape 4.5mm 75' Non-Conductive Tip, Large Case	75ft/22.8M
FTSP45-125NCT	63163701	SIMpull™ Fish Tape 4.5mm 125' Non-Conductive Tip, Large Case	125ft/38.1M
FTSP3-100NCT	63029901	SIMpull™ Fish Tape 3mm 100' Non-Conductive Tip, Medium Case	100ft/30.4M
FTSP3-240NCT	63029701	SIMpull™ Fish Tape 3mm 240' Non-Conductive Tip, Large Case	240ft/73.1M

\* When compared to Southwire™ Steel and Fiberglass fish tapes