

Fuses

- Replacement fuses for Fluke DMMs are available from your distributor in 440 mA, 500 mA, 630 mA, 1A, 2A, 3A, 11A, and 15A values. To order direct from Fluke call 1-888-99-FLUKE (U.S.) or contact your distributor.

| Model | Fuse Requirements |
|---|--|
| 21/23/75/77-II | P/N 871173; 630 mA 250V in series with either 871202; 3A 600V fuse or fusible resistor; R20 - DO NOT SUBSTITUTE FOR R20. P/N 892583; 15A 600V fuse. Also recommended replacement for units with a fused 10A input using a 20A fuse. |
| 21-III/75-III | P/N 871173; 630 mA 250V and P/N 803293 11A 1000V fuse |
| 76/29/79-II 83/85/87 (S/N < 65650001) | P/N 871207; 1A 600V fuse and P/N 892583; 15A 600V fuse |
| 25/27 | P/N 871173; 630 mA 250V fuse in series with P/N 871202; 3A 600V fuse. For units with 10A input using a 20A fuse, use P/N 892583; 15A 600V fuse. 27 CAT III S/N >7247001; P/N 943121 440 mA; 1000V fuse and P/N 803293; 11A 1000V fuse. |
| 45 (S/N < 7211001) | P/N 871181; 550 mA 250V fuse and P/N 892583; 15A 600V fuse |
| 73-II and 73-III | P/N 892583; 15A 600V fuse |
| 863/865/867/867B 83/85/87 (S/N > 65650001) | P/N 943121; 440 mA 1000V fuse and P/N 803293; 11A 1000V fuse |
| 87-IV/89-IV/187/189 83-III/85-III/87-III/87E-III 23-III/77-III/26-III/79-III 175/177/179 | |
| 111/112 | P/N 803293; 11A 1000V fuse |
| 712/713/714/715/ 716/717/718 | P/N 686527; 125 mA 250V fuse |