



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GB29 Burndy Connector

*Burndy LLC*

Catalog Number	GB29
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 2/0 Awg (Sol) -250 Kcmil, 1/2" Stud, 2 In Width.
Weight per unit	0.4800 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	COPPER ALLOY
----------	--------------

### Descriptions

Description	BURNDY CONNECTOR
extra long description	BUR GB29 2/0-250 CU-BAR 1 PC GRD
Long Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 2/0 AWG (Sol) -250 kcmil, 1/2" Stud, 2 IN Width.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable To 1/4 IN Thick Bar, Type GB Separates Cable From Bar, One-Wrench Installation, UL467 Listed, The High Copper Alloy Cast Body And DURIMUM Bolts, Nuts, And Lockwashers Make The GB And GBM Suitable For Direct Burial In Concrete Or Ground, Width: 2 IN, Installation Torque: 480 IN-LB, Height: 2 IN, Bar Thickness: 1/4 IN

### Manufacturer Information

Brand	BURNDY
GTIN	00781810231272
Manufacturers Part Number	GB29
UPC	781810231272

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GB

### Packaging

Carton	1
Weight Per each	0.48

### Uses, Certifications, and Standards

Application	For Copper Cable To Bar, Direct Burial Cable
standard	UL467