



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GBM26 2/0AWG Ground Conn *Burndy LLC*

Catalog Number	GBM26
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 4 Awg (Sol)-2/0 Awg (STR), 3/8" Stud.
Weight per unit	0.1500 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	COPPER ALLOY
----------	--------------

Descriptions

Description	2/0AWG GROUND CONN
extra long description	BUR GBM26 4SOL-2/0STR CU BAR 1 PC
Long Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), 3/8" Stud.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable To 1/4 IN Thick Bar, Type GBM Clamps Cable Directly On Bar Surface, One-Wrench Installation, UL467 Listed, The High Copper Alloy Cast Body And DURIMUM Bolts, Nuts, And Lockwashers Make The GBM Suitable For Direct Burial In Concrete Or Ground, Installation Torque: 240 IN-LB, Width: 1-1/2 IN, Bar Thickness: 1/4 IN, Height: 1-1/2 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810231449
Manufacturers Part Number	GBM26
UPC	781810231449

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GBM

Packaging

Carton	1
Weight Per each	0.15

Uses, Certifications, and Standards

Application	For Copper Cable To Bar, Direct Burial Cable
standard	UL467