



BURNDY Catalog Number
UPC Number
Description
Status

GBM34
7818102314633
300-500 CU BAR 1 PC GRD
Active

Web Use
BURNDY Product Line

Width (in)
Height (in)
Size (Hex) or Size (Bolt)
Thickness
Size (Hex) or Size (Bolt) - in
Width (Fraction)

Dimensional
2.22
2.32
1/2
0.25
0.50
2-2/9

Product Description

General
Mechanical Grounding Connector,
Cable to 1/4" Thick Bar, 300 kcmil
- 500 kcmil, 1/2" Stud

Bar Thickness (Range)
Copper Solid Size (Range)
Copper Stranded (Range)

Conductor(s)
N/A
N/A
300 kcmil-500 kcmil

Installation Torque
Type of Plating
Plated (Yes or No)
Product Material

Physical
480
Unplated
N
Copper Alloy

Rated for Direct Burial
UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Approvals / Certifications
Y
Y
Y
Exempt
N
N
UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175