

Specifications



Eaton GDB-5A

Eaton GDB Series Fast-acting fuse, 5A, 250 Vac or less, 32 Vdc (self certified)

General specifications

PRODUCT NAME	Eaton Bussmann series GDB fast-acting fuse
CATALOG NUMBER	GDB-5A
UPC	051712431835
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	0.7 g
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant CCC Marked CE Marked
CERTIFICATIONS	VDE
GLOBAL CATALOG	GDB-5A



Powering Business Worldwide

Product specifications

AMPERAGE RATING	5 A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE DROP	120 mV maximum
INTERRUPT RATING	50 AIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton GDB fast-acting glass tube fuses data sheet](#)

[Eaton Specification Sheet - GDB-5A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

