



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFRST20BK 20A Comm Self Test GFR Black *Hubbell Wiring Devices*

Catalog Number	GFRST20BK
Manufacturer	Hubbell Wiring Devices
Description	Gfci Receptacle, 20 A, 125 @ 60 HZ V Ac, 2 Poles, 3 Wires, #14 to #12 Awg Compatible Wire Size, Terminal Screws Connection, Screw Mount, 60 HZ, 1.75 In Length, 0.47 In Width, 3.27 In Height, Nylon (Face/Base) Material, Black, 0.3500 LB
Weight per unit	0.3500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Terminal Screws
Number of Wires	3-Wire Grounding
pallet quantity	2240
Phase	1
Poles	2-Pole
Wattage	2500
Wire Size	#14 to #12

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	20A COMM SELF TEST GFR BK
extra long description	HWDK GFRST20BK 20A COMM SELF TEST G

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778122095
series	Heavy Duty
UPC	883778122095

Taxonomies, Classifications, and Categories

Category Description	Commercial GFCI devices
Type	STANDARD

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	10
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

environmental conditions

Indoor Dry unless protected by additional means

Mounting

Screw Mount

standard

Meets All NEC® Requirements