



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GHB1040 40A GHB 1P BKR

Eaton Corp

|                  |                                                                                                                                                                                                 |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | GHB1040                                                                                                                                                                                         |
| Manufacturer     | Eaton Corp                                                                                                                                                                                      |
| Description      | Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Single-Pole, 40 A, 277 Vac, 125 VDC, 14 Kaic At 277 Vac, 50/60 HZ |
| Weight per unit  | 0.7000 (lbs/each)                                                                                                                                                                               |
| Product Category | 1 Pole                                                                                                                                                                                          |

### Features

|                  |                                   |
|------------------|-----------------------------------|
| Current Rating   | 40 A                              |
| dimensions       | 2.6300 IN X 1.0000 IN X 4.0000 IN |
| frame            | G                                 |
| interrupt rating | 14 kAIC at 277 Vac                |
| Poles            | Single-pole                       |
| Voltage Rating   | 277 Vac, 125 Vdc                  |

### Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                                                                           |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 40A GHB 1P BKR                                                                                                                                                                                                                                                                                                                                                                                            |
| extra long description | ETN GHB1040 40A GHB 1P BKR                                                                                                                                                                                                                                                                                                                                                                                |
| Features               | Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A. |
| Long Description       | Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Single-pole, 40 A, 277 Vac, 125 Vdc, 14 kAIC at 277 Vac, 50/60 Hz                                                                                                                                                                                                           |
| Product Type           | 40A GHB 1P BKR                                                                                                                                                                                                                                                                                                                                                                                            |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679023655 |
| Manufacturers Part Number | GHB1040        |
| UPC                       | 786679023655   |

### Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS  |
| Type                 | Molded case circuit breaker |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|        |   |
|--------|---|
| Carton | 1 |
|--------|---|

|                 |     |
|-----------------|-----|
| Weight Per each | 0.7 |
|-----------------|-----|

## Uses, Certifications, and Standards

|             |                                                                           |
|-------------|---------------------------------------------------------------------------|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies and<br>OEMs - Other |
|-------------|---------------------------------------------------------------------------|

|          |                                                         |
|----------|---------------------------------------------------------|
| standard | UL Listed,Federal Specifications Classification W-C375B |
|----------|---------------------------------------------------------|