



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GHB2050 Type GHB BRKR 2P 50A 277/480VAC Max 125/250VDC Max** *Eaton Corp*

|                  |                                                                                                                                                                                   |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | GHB2050                                                                                                                                                                           |
| Manufacturer     | Eaton Corp                                                                                                                                                                        |
| Description      | Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 50 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ |
| Weight per unit  | 1.1 (lbs/each)                                                                                                                                                                    |
| Product Category | 2 Pole                                                                                                                                                                            |

### **Features**

|                |                                   |
|----------------|-----------------------------------|
| Current Rating | 50 A                              |
| dimensions     | 2.6300 IN X 2.0000 IN X 4.0000 IN |
| frame          | G                                 |
| media          | Yes                               |
| Poles          | Two-pole                          |
| Voltage Rating | 480Y/277 Vac, 125/250 Vdc         |

### **Descriptions**

|                        |                                                                                                                                                                                                                                                                                                                                                                                                           |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | TYPE GHB BRKR 2P 50A 277/480VAC MAX 125/250VDC MAX                                                                                                                                                                                                                                                                                                                                                        |
| extra long description | ETN GHB2050 GHB CB 2P 50A 277/480VA                                                                                                                                                                                                                                                                                                                                                                       |
| Features               | Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A. |
| Long Description       | Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 50 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz                                                                                                                                                                                                                         |
| Product Type           | GHB CB 2P 50A 277/480VAC Max 125/250VDC                                                                                                                                                                                                                                                                                                                                                                   |

### **Manufacturer Information**

|                           |                     |
|---------------------------|---------------------|
| Brand                     | EATON CUTLER-HAMMER |
| GTIN                      | 00786679911235      |
| Manufacturers Part Number | GHB2050             |
| UPC                       | 786679911235        |

### **Taxonomies, Classifications, and Categories**

|                      |                             |
|----------------------|-----------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS  |
| Type                 | Molded case circuit breaker |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|        |   |
|--------|---|
| Carton | 1 |
|--------|---|

|                 |      |
|-----------------|------|
| Weight Per each | 1.05 |
|-----------------|------|

## Uses, Certifications, and Standards

|             |                                                                           |
|-------------|---------------------------------------------------------------------------|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies and<br>OEMs - Other |
|-------------|---------------------------------------------------------------------------|

|          |                                                         |
|----------|---------------------------------------------------------|
| standard | UL Listed,Federal Specifications Classification W-C375B |
|----------|---------------------------------------------------------|