



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GK350400N 3-1/2" & 4" Neo Gasket *Appleton/Oz Gedney*

|                  |   |
|------------------|---|
| Catalog Number   | GK350400N   |
| Manufacturer     | Appleton/Oz Gedney  |
| Description      | Appleton Form 35 Malleable Iron Unilet Cover Gasket, Body Size:<br>3-1/2 4 In, Material: Neoprene |
| Weight per unit  | 0.0096 (lbs/each)   |
| Product Category | Bodies & Covers   |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 3-1/2" & 4" NEO GASKET  |
| extra long description | APP GK350-400-N FORM 35 UNILET NEO  |
| Long Description       | Appleton Form 35 Malleable Iron Unilet Cover Gasket, Body Size:<br>3-1/2 4 IN, Material: Neoprene |
| Product Type           | Form 35 Unilet Neo GSKT 3-1/2 to 4 In   |
| Special Features       | Neoprene. Tear out inner section to convert to "open" type<br>gasket.                             |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Appleton       |
| GTIN                      | 00781381435109 |
| Manufacturers Part Number | GK350-400-N    |
| UPC                       | 781381435109   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | FORM 5 CONDULETS, COVERS, & GASKETS              |
| Type                 | Solid gasket for use with Form 35 conduit bodies |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 25     |
| Weight Per each | 0.0096 |

### Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | For use with 3.50 and 4.00 inch Form 35 Conduit bodies. Seals<br>and protects.                  |
| standard    | UL Standard: 514A 514B, UL Listed: E2527, CSA Standard: C22.2<br>No.18.3, CSA Certified: 065183 |