



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GLL12 6" Ground Bushing 105 C Ins 3 to 6 Al Lug

*Crouse-Hinds*

Catalog Number	GLL12
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series GLL Grounding Bushing, Rigid/Imc, Aluminum Lug, #3/0-6 Awg, Malleable Iron, 105°C Temperature Rating, Threaded, 6"
Weight per unit	2.0 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Threaded
dimensions	8.9000 IN X 1.3000 IN X 8.8000 IN
Material	Malleable Iron Body, Plastic Throat Liner

### Dimensions and Weight

Size	6 In
------	------

### Descriptions

Description	6" GROUND BUSHING 105 C INS 3 TO 6 AL LUG
extra long description	MIDWEST GLL 12 6 GRND BUSH 105C INS
Features	Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing.
Long Description	Eaton Crouse-Hinds series GLL grounding bushing, Rigid/IMC, Aluminum lug, #3/0-6 AWG, Malleable iron, 105°C temperature rating, Threaded, 6"
Product Type	6 GRND Bush 105C Insul 3 to 6 Al Lug
Special Features	With 6 To 3/0 AWG Aluminum Lug for Copper/Aluminum Grounding Conductor, Weight 160 Lb per 100

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564123121
Manufacturers Part Number	GLL 12
UPC	784564123121

### Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Grounding bushing

### Packaging

Carton	1
Weight Per each	2



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, CSA
Temperature Rating	105 DEG C