



Powering Business Worldwide

pe.eaton.com

Fast-Acting Fuse

BK/GMA-1.5-R

UPC:051712647175

Dimensions:

- **Height:** .788 IN
- **Length:** .197 IN
- **Width:** .197 IN

Weight:.002 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 1.5A
- **Voltage Rating:** 250 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 10 kAIC at 125 Vac, 0.1 kAIC at 250 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** out axial leads
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end
- **Quantity:** Bulk 100

Supporting documents:

- [GMA 1.5A BUSS FA BK 100 BOX -R](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant



