

Specifications



Eaton GMA-3-R

GMA 3A BUSS fuse, 3-R

General specifications

PRODUCT NAME	Eaton Bussmann series GMA fast-acting fuse
CATALOG NUMBER	GMA-3-R
UPC	051712647946
EAN	5027590501774
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	0.7 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant

Product specifications

AMPERAGE RATING	3 A
INTERRUPT RATING	10 kAIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 2 min at 200%
MATERIAL	Nickel-plated brass endcaps Glass tube
PACKAGING TYPE	Standard
VOLTAGE RATING	32 Vdc (self certified)
TYPE	Electronic- small dimension
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
GMA-3-R](#)

[Eaton GMA time delay
glass tube fuses data
sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

