



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GP6429  
 7818102605555  
 2/0SOL-250, 3/8 IPS 2 CO  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Width (in)	2.12
Height (in)	2.88
Size (Hex) or Size (Bolt)	3/8
Size (Hex) or Size (Bolt) - in	0.38
Width (Fraction)	2-1/8
Height (Fraction) (in)	2-7/8

**General**

**Product Description**  
 Mechanical Grounding Connector,  
 2 Cables to Rod or Pipe, 2/0 AWG  
 (Sol) -250 kcmil, 3/8" Pipe,  
 5/8" -3/4" Rod, 3/8" Stud

**Conductor(s)**

Copper Tube Size (SCH40) - Range	5/8-3/4
Rod Size (Range)	5/8 in-3/4 in
Copper Solid Size (Range)	2/0-4/0
Copper Stranded (Range)	1/0-250

**Physical**

Installation Torque	240
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Copper Alloy

**Approvals / Certifications**

UL Listed	Y
CSA Certified	N
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467
Rated for Direct Burial	Y

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175